



Click-N-Seal™ Self-Torquing Adaptors

Thread to barb connections that can't be overtightened!

- For 1/16, 1/8 or 3/32" ID softwall tubing
- For 1/4"-28 UNF or M6 threaded ports
- Re-useable and reliable

Click-N-Seal™ allows you to feel and hear when the fitting is properly installed, giving an audible click when the correct torque is reached. This thread to barb adaptor version enables connection of softwall tubing to a threaded port.


Ordering information

CLICK-N-SEAL™ MALE 1/4"-28 UNF TO BARB ADAPTOR


PART NUMBER	MATERIAL	COLOR	THREAD	TUBE ID	QTY
008NB16-CS5B	PC	Black	1/4•28 M	1/16" (1.57mm)	10pk
008NB16-CS5H	PC	White	1/4•28 M	1/16" (1.57mm)	10pk
008NB16-CS5R	PC	Red	1/4•28 M	1/16" (1.57mm)	10pk
008NB16-CS5B	PC	Black	M6	1/16" (1.57mm)	10pk
008NB16-CS5H	PC	White	M6	1/16" (1.57mm)	10pk
008NB16-CS5R	PC	Red	M6	1/16" (1.57mm)	10pk
008NB32-CS5B	PC	Black	1/4•28 M	3/16" (3.2mm)	10pk
008NB32-CS5H	PC	White	1/4•28 M	3/16" (3.2mm)	10pk
008NB32-CS5R	PC	Red	1/4•28 M	3/16" (3.2mm)	10pk
008NB32-CS5B	PC	Black	M6	3/16" (3.2mm)	10pk
008NB32-CS5H	PC	White	M6	3/16" (3.2mm)	10pk
008NB32-CS5R	PC	Red	M6	3/16" (3.2mm)	10pk
008NB40-CS5B	PC	Black	1/4•28 M	5/32" (4.0mm)	10pk
008NB40-CS5H	PC	White	1/4•28 M	5/32" (4.0mm)	10pk
008NB40-CS5R	PC	Red	1/4•28 M	5/32" (4.0mm)	10pk

CLICK-N-SEAL™ ULTRA MALE 1/4"-28 UNF TO BARB ADAPTOR

008NB16-KT5L	PEEK™	Natural	1/4•28 M	1/16" (1.57mm)	10pk
008NB16-KT6L	PEEK™	Natural	1/4•28 M	1/16" (1.57mm)	10pk
008NB32-KT5L	PEEK™	Natural	1/4•28 M	3/16" (3.2mm)	10pk
008NB32-KT6L	PEEK™	Natural	1/4•28 M	3/16" (3.2mm)	10pk



008NBxx¹-CS Series
Click-N-Seal™ Thread to Barb




008NBxx¹-KT Series
Click-N-Seal Ultra™ Thread to Barb

Microbarb

Low-carryover connection for softwall to semi-rigid tubing

MicroBarb provides a secure, low-carryover connection between flexible soft tubing and semi-rigid tubing. Two components ensure that the both the ID and OD of the soft tubing are firmly gripped, ensuring a secure connection. The barbed component fits inside the tube ID and creates a flat surface for connection. The threaded outer connector slips over the tubing OD and secures the barb in place, creating a female threaded flat-bottom port.




PEEK™ construction gives a chemically inert and robust connection. Simply locate the tube ID and OD in the table below to identify the MicroBarb part number for your application. For special tubing sizes, please call the factory to see if we have a Microbarb combination to suit your needs.

MicroBarb connections are also sized for common peristaltic pump tube sizes. These tubes use color-coded stops to indicate the size and type of tube.

Ordering information

TUBE OD	TUBE ID		
	0.01	0.02	0.03
0.062"	Call factory	Call factory	Call factory
0.082"	008MB025-208K2L ORG-BLU	Call factory	008MB076-208K2L
0.092"	008MB025-234K2L	008MB051-234K2L ORG-YEL	Call factory
0.104"	Call factory	008MB051-264K2L	008MB095-263K2L WHT-BLK



008MB Series
Microbarb™ Thread to Barb

¹The nut dimensions shown apply to all variants within the product group. Barb diameters and lengths vary according to the ID of tube.